

The PCM500 Fluid Cleanliness Monitor is a portable diagnostic monitoring device that provides a measurement of system fluid cleanliness.

As the successor to the popular PCM400, the new improved PCM500 uses proven mesh blockage technology to report accurate, reliable, 3 part ISO 4406 cleanliness codes for most types of fluids, in many types of environment.

With the PCM500 you can:

- Monitor contamination levels in mineral, synthetic, or water based fluids. Results are unaffected by the presence of water, air, or dark fluids
- Get accurate, 3 part* ISO 4406 cleanliness code results in under 6 minutes and to quickly take preventative action
- Upload real-time results directly to mobile devices for analysis and action
- 'Pass off' cleanliness of new builds quickly and confidently
- Protect your systems from catastrophic failure by detecting abnormal fluid cleanliness conditions quickly

The PCM500 can be permanently installed to monitor critical applications (including component test facilities) or used as a portable device for routine condition monitoring of various fluid systems

PCM500 Monitor Features

- Proven mesh blockage technology provides accurate 3-part* ISO 4406, AS 4059 Table 1 (NAS 1638) or AS 4059 Table 2 cleanliness codes
- Self cleaning procedure between each test ensures optimum accuracy of results
- Compact, robust, fully self contained portable design (fluid sampling pump included)
- Simple to use, color touch screen interface
- Long battery life for extended operation in remote locations
- Measurement of fluid cleanliness, temperature, viscosity, and optional water content.

*3 part code measured at 4 $\mu\text{m},$ 6 μm and 14 μm (c) per ISO 16889.

New: PCM500 Series Fluid Cleanliness Monitor



Operation

The color LCD touch screen allows simple menu driven input of sample identification, monitor configuration and data output.

The HD screen displays real time data and test results which are automatically stored for subsequent trending and evaluation. An optional bluetooth connected printer allows the operator to produce a hard copy of the test results if required.

All ancillary components for high and low pressure on-line sample monitoring are contained

within the unit, with sufficient internal power to complete up to 35 tests between charges. (AC power can be used if preferred).

For further protection and ease of transport, the PCM500 is supplied in a robust flight case.



Specifications

Power supply:	90-260 VAC or integral 12 VDC Lithium Ion battery
Battery life:	Typically 35 samples
Temperature Range:	10 °C to 80 °C (50 °F to 176 °F) (dependent on fluid type)
Compatibility:	Water glycols, aqueous solutions. Petroleum and synthetic oils (hydraulic lubricating, dielectric, etc.), fuels, industrial phosphate esters.
Seals:	Fluorocarbon
Operating Viscosity:	1.5 to 450 cSt (30 to 2,200 SUS)
Pressure:	0 to 315 bar (4570 psi) max
Monitoring range:	ISO 4406: <11/9/7 to 23/21/17
	SAE AS 4059 Table 1
	Class 1 to 12 (derived from NAS 1638) SAE AS 4059 Table 2 >4 µm 1A to 12A, >6 µm 1B to 12B >14 µm 1C to 12C
Water in Oil % RH:	Class 1 to 12 (derived from NAS 1638) SAE AS 4059 Table 2 >4 µm 1A to 12A, >6 µm 1B to
Water in Oil % RH: Accuracy:	Class 1 to 12 (derived from NAS 1638) SAE AS 4059 Table 2 >4 µm 1A to 12A, >6 µm 1B to 12B >14 µm 1C to 12C
	Class 1 to 12 (derived from NAS 1638) SAE AS 4059 Table 2 >4 µm 1A to 12A, >6 µm 1B to 12B >14 µm 1C to 12C ± 2% at 5 to 95% RH (PCM500W)
Accuracy: Communication	Class 1 to 12 (derived from NAS 1638) SAE AS 4059 Table 2 >4 µm 1A to 12A, >6 µm 1B to 12B >14 µm 1C to 12C ± 2% at 5 to 95% RH (PCM500W) ± 1/2 ISO 4406 Code 3 x USB's (Data Acquisition, PC Setup, Printer), Ethernet and
Accuracy: Communication Ports:	Class 1 to 12 (derived from NAS 1638) SAE AS 4059 Table 2 >4 µm 1A to 12A, >6 µm 1B to 12B >14 µm 1C to 12C ± 2% at 5 to 95% RH (PCM500W) ± 1/2 ISO 4406 Code 3 x USB's (Data Acquisition, PC Setup, Printer), Ethernet and RS232C (PLC Control)



Real time data is displayed during test to show progress



Multiple test data can be stored and displayed for subsequent analysis and download

Ordering information

Please select from the following part number options only.

Without Water Sensor	With Water Sensor
PCM500 M A	PCM500W M A
PCM500 M B	PCM500W M B
PCM500 M D	PCM500W M D
PCM500 U B	PCM500W U C
PCM500 U C	PCM500W U D
1 2	1 2

References 12 refer to tables below.

Table 1: Fitting Type

Code	Description
Μ	1/4" BSPP Female Swivel fitting to metric test point
U	1/4" NPT fitting and end cap

Table 2: Power Lead

Code	Description
А	UK Power Lead
В	European Power Lead
С	USA Power Lead
D	Australian Power Lead

Printer Kit and Accessories

PCM500-PRT





Pall Machinery and Equipment

25 Harbor Park Drive Port Washington, NY 11050 +1 516 484 3600 telephone +1 800 289 7255 toll free US

Portsmouth - UK +44 (0)23 9233 8000 telephone +44 (0)23 9233 8811 fax industrialeu@pall.com





Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/contact

Because of technological developments related to the products, systems, and/or services described herein, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2015, Pall Corporation. Pall and PALL are trademarks of Pall Corporation. ® Indicates a trademark registered in the USA. Better Lives. Better Planet and *Filtration. Separation. Solution.sm* are service marks of Pall Corporation.